



### FULLY SUPERVISED

Pendants communicate with base station every 13 hours to ensure proper connection. Central station is contacted in the event of a power outage, low battery or loss of RF signal. Central Station is contacted every 52 hours if 4 tests are missed.



### AUDIBLE PROMPTS

Audible prompts can be heard during system set-up, system programming, testing and full system check. English, Spanish and French voice prompts are standard.



### SOS CALL

Emergency call is placed by either pressing the 'EMERGENCY' button on the pendant or on the base unit. Braille lettering is included on the base unit buttons.



### BATTERY BACK-UP

Base unit includes rechargeable batteries for up to 24 hours of emergency battery power in the event of a power outage.



### CARETAKER BUTTON

Program an additional phone number to call family, friend or a nurse assist hotline. The programmed number is called only upon activation from the 'CARETAKER' button on the base unit.

## Are you concerned about your loved one's safety?



Of the 35 million Americans over 65, about 1 in 3 will fall in a given year.



Seniors are hospitalized for fall-related injuries 5 times more often than they are for other injuries.



50% of people who fall require assistance from someone else to get up.



608 E Congress St.  
Nora Springs, IA 50458  
641-749-2531

# Medical Alert



with a  
**TWO-WAY VOICE PENDANT**

**Speak to the central station through the pendant even while out in the yard!**



***NOW You have even MORE  
Choice with the***



## ***TWO-WAY VOICE PENDANT***

Speak and hear clearly through the pendant with the Central Station from anywhere around your home!



### **BASE KIT Item #41911**

- Dials and provides voice communication with Central Station
- For use with Two-Way Voice Pendant, Emergency Wall Communicator or Cellular Accessory

### **Features of the Two-Way Voice Pendant Item #41915**

- Dials and provides voice communication with Central Station
- Water resistant
- Up to 4 hour talk and 6 month standby times
- Up to 600' range
- Can be worn on lanyard, wrist or on belt

